

# Compatibility list for the premium neutral silicone

## OTTOSEAL® S 110

### Compatibility list for the premium neutral silicone OTTOSEAL® S 110

Tests in compliance with ift directive D1 01/1 Suitability of sealants – Part 1 : Testing of materials in contact with the insulating glass edge sealing, February 2008

Test method: Three phase test P1, chapter 4.1

Transparent silicone sealant may become yellowish from contact with the secondary edge sealing.

The following list encompasses the products which are compatible with OTTOSEAL® S 110:

OTTOSEAL® S 110		
Manufacturer	Primary sealant	Secondary sealant
IGK Isolierglasklebstoffe GmbH, Hasselroth	IGK 511	IGK 130, IGK 311, IGK 330
Fenzi Spa, Tribiano	Butylver	Thiover, Poliver
Kömmerling Chemische Fabrik GmbH, Pirmasens	GD 115	GD 116, GD 677
Tremco Illbruck GmbH & Co. KG, Bodenwöhr	JS 880	JS 442
Hutchinson GmbH, Eschborn	Totalseal 3524/1	Totalseal 3189/2
others	--	IG silicone

This information has been compiled on the basis of extensive tests and to our best knowledge taking in account the actual status of experiences in practice. The statements, however, only refer to the tested material and the test conditions taken as a basis. By way of precaution we would like to point out that the findings from tests carried out in the lab cannot cover all possible influences in practice nor all possible ways of mounting. Our advice is to always check the suitability of the sealant for the application at hand on a sample or prototype.



**Sealants • Adhesives**

Hermann Otto GmbH · Krankenhausstr. 14 · 83413 Fridolfing, GERMANY

Tel.: 0049-8684-908-0 · Fax: 0049-8684-1260

E-mail: info@otto-chemie.de · Internet: www.otto-chemie.com